




PRESSALIT®

Product Item number	CareSystem shower chair 410 with aperture, manually height and sideways adjustable R7567000
Colour Product description	White  Shower chair 410 with aperture, "soft feel", with back rest, seat height adjustable 330 mm, for mounting on horizontal track. Discontinued as per 31/12-2015 Shower chair 410 with aperture, "soft feel", with back rest, seat height adjustable 330 mm, for mounting on horizontal track. Discontinued as per 31/12-2015
Adjustability Product capacity	Height and sideways adjustable Max. vertical load: 150 kg.
Materials Ergonomy	Basic material: 20 micrometre anodized aluminium Seat/backrest: Polyurethane foam with marine ply core Seat/backrest surface: Gum lac Lever: Stainless steel w/nylon knob Front plate/end covers, track: Polystyrene plastic (PS) Soft and slip-resistant material that has a warm feel. Ergonomically designed seat with aperture that makes intimate hygiene easier.



PRESSALIT®

Product Item number	CareSystem shower chair 410 with aperture, manually height and sideways adjustable R7567000
Features	<p>The seat can fold up when not in use or to make more space.</p> <p>Height adjustable 330 mm - the height of the seat and the backrest can be adjusted separately.</p> <p>Can be pushed along the track.</p>
Cleaning	Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in clear water.

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®