



| | |
|---|--|
| Product Item number | CareSystem support arm with spring height adjustable RF306000 |
| Colour | White |
| Product description | <p>Support arm with spring counter balance, 600 mm, height adjustable without vertical track. Excl. mounting kit. Discontinued as per 31 Dec 2015</p> <p>Support arm with spring counter balance, 600 mm, height adjustable without vertical track. Excl. mounting kit. Discontinued as per 31 Dec 2015</p> |
| Adjustability Product capacity | <p>Height adjustable</p> <p>Max. vertical load: 135 kg.</p> |
| Materials | <p>Basic material: 20 micrometre anodized aluminium</p> <p>Surface material: Two-component plastic (PVC)</p> <p>End cap: Arnite</p> |
| Ergonomy | <p>The oval shape gives an easy and comfortable surface to lean and push against.</p> <p>The end of the support arm is enlarged so that it is easier to pull forward from a sitting position and also provides a clear sense of where the support arm ends.</p> <p>The surface material is soft and slip-resistant, and has a warm feel.</p> |



PRESSALIT®

| | |
|--------------------|---|
| Product | CareSystem support arm with spring height adjustable |
| Item number | RF306000 |
| Features | <p>The spring ensures that the support does not "fall" down from its vertical position, and it makes raising easier. A counterbalanced support arm can be raised and lowered with a sliding movement or in easy stages. Folds against the wall.</p> <p>Height adjustable 250 mm.</p> <p>The underside is shaped for the mounting of various accessories.</p> <p>Without vertical track.</p> |
| Cleaning | <p>Pressalit recommends that chalky deposits be removed from wall tracks and other aluminum parts using a solution of three parts of 30% acetic acid to seven parts tap water. When the aluminum parts have been washed down with this solution, the parts should be wiped over with a damp cloth wrung out in clear water.</p> |

pressalit.com

Pressalit A/S
Pressalitvej 1
DK-8680 Ry
Tel.: +45 8788 8788
Fax: +45 8788 8789
E-mail: pressalit@pressalit.com

PRESSALIT®